

IDEAL SUPER GLOSS ENAMEL

PRODUCT DESCRIPTION AND USES.

Ideal Super Gloss Enamel is formulated with Alkyd resin and Poly Urethane resin to provide maximum durability with a high gloss level and excellent gloss retention. It is suitable for use in any weather conditions including high humidity regions and areas of high rainfall. Ideal Super Gloss Enamel gives excellent flexibility, opacity and light fastness(non-fading). It can be used both internally and externally on wood, metal, plaster, gypsum boards, stonework etc. Ideal Super Gloss Enamel should be applied over appropriately primed and undercoated surfaces.

SURFACE PREPARATION

New surfaces

Surfaces should be clean, dry and free of any loose and flaky materials.

Step 1: Apply 1 coat (appropriate) primer

Step 2: Apply 1 coat Ideal Universal Undercoat

Step 3&4: Apply 2 coats Ideal Super Gloss Enamel

Lightly abrade between coats. Allow 12-15hours drying between each coat.

Previously painted surfaces

Ensure the surface is clean, dry and free from loose and flaky materials. Patch prime as necessary with the appropriate primer.

Step 1: Apply one coat Ideal Universal Undercoat

Step 2&3: Apply 1-2 coats Ideal Super Gloss Enamel. Lightly abrade between coats. Allow 12-15 hours drying between coats.

FINISH

High gloss

APPLICATION

By brush, roller or airless spray.

THINNING AND MIXING

Thin with white spirit to the required consistency.

EQUIPMENT CLEANING

Clean equipment immediately after use with white spirit.

DRYING TIME

Touch dry 4 hrs. Recoatable after 16 hrs.

COLOUR RANGE

Brilliant White, BS 4800 Colour range, Ideal Classic Colour range & all NCS colours

SPREADING CAPACITY.

Approximately 11-14 m² per litre on a smooth surface at approx. 30/40 microns DFT.

PACK SIZES

1 litre, 4 litres & 20 litres.